

ESCAPE SOLUTIONS
North Mouthbit Respirators

- Mouthbit respirators offer a quick and economical method to escape non-IDLH emergency situations
- Large, soft and flexible nose pads hold securely without pinching
- Wider nose clip fits a variety of facial types
- Silicone mouthpiece is more comfortable to wear over long periods
- Packed in sealable plastic bag, carrying bag sold separately (79BAG)

SKU	Description	Packaging
7902	Acid gas mouthbit respirator for protection from atmospheres containing Chlorine, Hydrogen Chloride, Sulfur Dioxide, Hydrogen Sulfide, (escape) Chloride Dioxide, Hydrogen Fluoride	Each
7904	Ammonia mouthbit respirator. For protection from atmospheres containing ammonia	Each


NORTH
by Honeywell

North CBRN Respirators

- Emergency escape respirator is NIOSH approved CAP 2 for minimum of 30 minutes of protection for escape from non-IDLH atmospheres.
- Easy to use and universally sized
- Dual cartridge design are strategically located to keep out of line of site
- Translucent polyurethane hood allows for full vision and is less-claustrophobic

SKU	Description	Packaging
ER2000CBRN	Emergency Escape CBRN Respirator, complete Escape hood assembled in sealed inner bag, within nylon carry bag	Each

Replacement Components

ERBAG	Replacement black nylon carry bag for ER2000CBRN	Each
ERTRAIN	Training Kit includes 1 set of labels for ER2000	1 per package



ER2000CBRN

NORTH
by Honeywell

North Escape Breathing Apparatus (EBA)

- Transparent polyurethane hood is less claustrophobic
- Air deflector directs air to front of hood and away from workers' eyes
- Pictogram instructions on carrying bag can be understood in any language
- 42 lpm of breathing air is higher than many units so worker is less likely to over breathe
- High visibility carrying bag

SKU	Description	Packaging
845	5 minute breathing time EBA; bright yellow carrying bag	Each
850	10 minute breathing time EBA; bright orange carrying bag	Each
89992	Molded carry case for 845 Five Minute EBA	Each
89987	Molded carry case for 850 Ten Minute EBA	Each



845 and 850

Sperian Survivair Escape Breathing Apparatus (EBA)

- Features a valve and pressure gauge assembly, breathing tube, protective air hood and regulator assembled in a carry pouch for added convenience
- Hood fits easily over eye glasses
- Flexible hood has a large opening with drawstring, offering a proper fit to wearers
- Clear tuftane film hood with a permanent anti-fog coating

SKU	Description
975080	Survivair 5-Minute Escape Breathing Apparatus (EBA-5)
975090	Survivair 10-Minute Escape Breathing Apparatus (EBA-10)
975163	Sperian EBA-5/10 Min, Molded Case
975081	Spare Cylinder (2216 psig, Aluminum), 5-Minute EBA and Hip-Pac
975091	Spare Cylinder (3000 psig, Aluminum), 10-Minute EBA

Sperian is now Honeywell



975090

FIT TESTING

For most applications a qualitative fit test will be sufficient. Irritant Smoke creates a positive reaction of coughing if there is breakthrough. Bitrex uses a nebulizer to spray a bitter substance inside a hood. Since Bitrex requires N95 type filters, it is the preferred method for qualitatively fit testing disposable filtering facepieces (dust masks). It can also be used to fit test the CFR-1 and the 7190.

Which Fit Test Method is Best for You?


Qualitative Fit Test Kits

A choice of portable fit test kits is available for fitting employees in the right size mask using qualitative fit testing. Select from Irritant Smoke or Bitrex® kits. Deluxe kits include a hard case. The Irritant Smoke Deluxe Kit also includes a training video. The VeriFit® irritant smoke kit features a handy cassette and includes 10 easy to use, plastic smoke tubes.

Quantitative Fit testing

Quantitative Fit testing provides an absolute number, telling you how well a mask fits on an individual. These tests can be performed using either a particle count such as the TSI Porta-Count® or a negative pressure method.

Quantitative Fit Test Kit for CFR-1

The CFR-1 fit test kit contains one each of small, medium and large 4200 masks, probed to perform quantitative fit testing. 100 refresher wipe pads plus extra suction cups and tubes for fit testing are also included. The rugged storage case keeps contents secure and readily available when needed. The 4200QNKT is used in conjunction with a PortaCount® fit tester with the N95 companion.

**Economy Fit Test Kits are not available in U.S. or Mexico*

North Fit Test Kits

SKU	Description
193120	Saccharin fit test kit
770039E	Bitrex fit test kit, economy
770039	Bitrex fit test kit, deluxe
770046	Irritant smoke fit test kit, 6 smoke tubes
770040E	Irritant smoke fit test kit, economy
770040	Irritant smoke fit test kit, deluxe
193140	Isoamyl Acetate (IAA) fit test kit
194040	Isoamyl Acetate (IAA) fit test kit, deluxe

Quantitative Fit Test Adapter

SKU	Description
770021	For North 5500, 7700, 5400 and 7600 Series facepieces

Sperian Fit Test Kits

SKU	Description
420025	Quantitative fit test adapter for Opti-Fit facepieces with S-Series cartridges
769095	Quantitative fit test adapter for Opti-fit CBRN gas mask



193120



770039E



770040E



194040

Call Customer Care at 800 430-5490.

Call Customer Care at 800 430-4110.

ACCESSORIES



80100

Sperian is now Honeywell



80836A

North Eyewear and Accessories

SKU	Description
80100	Eyeglass frame for North 5400, 7600 and 7800 Series full facepieces. Plastic, no lenses
760023	Eyeglass frame for North 5400, 7600 and 7800 Series full facepieces. Metal, no lenses
760024	Eyeglass frame for North 5400, 7600 and 7800 Series full facepieces. Metal with spring, no lenses
962260	Eyeglass frame for Opti-Fit facepieces including tactical and CBRN, no lenses
80836A	Cover lens, peel-away, clear, for North 5400, 7600 and 7800 Series full facepieces. Three sheets per set, 5 sets per pack
PA105	Cover lens, peel-away, clear, for North Primair 100 Series hoods PA111, PA121, PA131 and PA141. Three sheets per set, 5 sets per pack
PA106	Cover lens, peel-away, clear, for North Primair FM 200 and 300 Series hoods. Three sheets per set, 5 sets per pack

Sperian Eyewear and Accessories

SKU	Description
702028	Cover lens, peel-away, clear, for Opti-Fit facepieces including tactical and CBRN. 25 per box
702019	Cover lens, peel-away, tinted for Opti-Fit facepieces including tactical. 25 per box

Voice Amplifier

The 7600VA Voice Amplifier is designed to clip onto the 7600 Series full facepiece speaking diaphragm housing and easily installs in a few seconds. This compact, battery-operated unit clearly amplifies and projects the wearer's voice, allowing for clear and crisp speech, even in areas with high ambient noise.

SKU	Description
7600VA	Voice Amplifier for 7600 Series full facepiece



7600VA



Call Customer Care at 800 430-5490.



Call Customer Care at 800 430-4110.

ACCESSORIES

Cleaning and Sanitizing

Sperian is now Honeywell

Refresher wipe pads provide a quick, easy method of removing perspiration and body oils from the respirator facepiece between scheduled cleanings.

These wipe pads make respirator usage more acceptable to the wearer by improving comfort. Shockwave™ is a disinfectant and cleaner that may be used to clean all reusable facepieces and their replacement parts. This concentrated liquid will make just the right amount of sanitizing solution for your needs when mixed with warm water. Each ounce will make one gallon of detergent that will sanitize, disinfect and deodorize surfaces.

SKU	Description	Packaging
7003	Refresher wipes with alcohol, 5" x 7"	Individually wrapped, 100 per box
7003L	Refresher wipes with alcohol, 8" x 10"	Individually wrapped, 100 per box
7003A	Refresher wipes, alcohol free, 5" x 7"	Individually wrapped, 100 per box
7003AL	Refresher wipes, alcohol free, 8" x 10"	Individually wrapped, 100 per box
80944A	Anti Fog wipes for North facepieces	Individually foil packaged, 10 per box
80995	Cleaner and disinfectant for respirator facepieces	10 oz. bottle
140082	Refresher wipes	Canister of 220 wipes
981803	Anti Fog wipes for Sperian facepieces	100 per box
981808	Anti Fog wipes, dry, for Sperian facepieces	100 per box



140082

Storage

OSHA and CSA require respirators to be stored in a clean and contaminant free environment. Protect your workers and your respirators by storing them properly.

SKU	Description
79BAG	Nylon carrying bag North CFR-1, 7190 and mouthbit respirators
77BAG	Nylon carrying bag half masks
76BAG	Nylon carrying bag full facepieces
200101	Tote Bag
CA133	Molded carrying case for North Compact Air PAPR
89986	Wall mount bracket for EBA
83219	Wall Case, deluxe unit with shelf, for single SCBA
940118	Zipper storage bag for half masks and full facepieces



79BAG



76BAG